








ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE


NOTES:

- MATERIAL:
INSULATOR: HIGH TEMPERATURE THERMO PLASTIC
FLAMMABILITY RATING: UL94V-0 COLOR: BLACK
CONTACT: COPPER ALLOYS
COVER: STAINLESS STEEL
- CONTACT AREA PLATING: GOLD OVER NI
- SOLDER TAIL COPLANARITY MUST BE WITHIN 0.10MAX.
- OPERATING TEMPERATURE : -40°C TO +85°C.



PAD AREA
KEEP OUT AREA

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05




TF CARD PIN DEFINE			
PIN NO.	NAME	TYPE	DESCRIPTION
1	DATE	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(BIT1)

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD		
DRAWING			TITLE SD卡/存储卡卡座T1.9(翻盖式) REV. A		
CHECK					
APPROVAL					
TOLERANCES ARE			PART NO. LAIL-TF09-T1.9-F UNITS mm		
30-150	±0.35	ANGLE ±3°			
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
			DWG.NO.		
			Projection 		


ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE




NOTES


1. NUMBER OF CONNECTORS:1000PCS/REEL
2. LEAD TAPE LENGTH



3.QUANTITY:10000PCS/CARTON



上下各1PCS珍珠棉



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	SD卡/存储卡卡座T1.9(翻盖式)	REV.	A
30-150	±0.35	PART NO.	LAIL-TF09-T1.9-F	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
		DWG.NO.		Projection	