





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- Notes:
- 1.Material:
Housing: High Temperature Thermoplastic
Terminal:Copper Alloy
Shell: Stainless Steel
- 2.Plating:
Terminal:50u" Ni Underplated Overall
G/F Plated On Contact Area
G/F Plated On Solder Area
Shell:30u" Ni Underplated Overall
G/F Plated On Contact Area And solder Area
- 3.Technical Speciality:
Rated Voltage: 30V
Current Rating: 0.5A
Insulation Resistance:1000MΩ Min.
Contact Resistance:100mΩ Max.
Withstanding Voltage: 500V DC For 1 Minutes.
Operating Temperature: -40~+85℃ Humidity 80% R.H Max.




COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD					
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	SIM卡卡座T1.25（自弹式）	REV.	A		
30-150	±0.35	PART NO.	LAIL-SIM015-T1.25-T	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection			
±3°							

ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE

Direction of use



NOTES:

- 1.Packing quantity per plate: 2000PCS/Plate
- 2.Loading and packing method




3.Total packaging:20000PCS/Box

Carrier Tape

Direction of use

DETAIL B


DETAIL B



10-REEL

The bottom and top of the carton
Pad it with apiece of pearl cotton

BOX
350*350*340mm



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLESIM卡卡座T1.25（自弹式）REV.A			
CHECK					
APPROVAL					
TOLERANCES ARE		PART NO.	LAIL-SIM015-T1.25-T	UNITS	mm
30-150	±0.35	ANGLE ±3°	DWG.NO. Projection		
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				