







ROHS



PCB LAYOUT(TOP VIEW)

(T=1.60mm)

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

备注:

1) 材质:

1-1 本体:LCP 94V-0 黑色

1-2 端子:C2680

1-3 外壳:C2680或SPCC

2) 镀层:

2-1 端子:所有面镀镍, 接点镀金(镀金G/F u”+50u”锡MIN), 焊脚镀锡50u”MIN,

3) 技术规格

3-1. 额定电压:40V

3-2. 额定电流:0.5A

3-3. 绝缘电阻:100兆欧最小

3-4. 接触电阻:30毫欧最大

3-5. 操作温度:-20度到85度

3-6. 插入力:44.1N Max

3-7. 拔出力:9.8~44.1N;

3-8. 耐久:10000次

4	STOPPLE	1	LCP	UL94V-0,BL
3	SHELL	1	C2680R&SPCC	PLATED NI
2	HOUSING	1	LCP	UL94V-0,BL
1	CONTACT	21	C2680R-H	PLATED Au
NO.	ITEM	Q'TY	DESCRIPTION	FINISH

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING		TOLERANCES ARE				
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	HDMI-A连接器19PIN母端立贴	REV.	A	
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-HDMI-A03-A-LT	UNITS	mm
10-30	±0.2		DWG.NO.		Projection 	
5-10	±0.15					
0-5	±0.1					