









ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



PCB.WELDING DRAWING (TOLERANCE:±0.05)

Main technical performance	
Rated electrical load	DC 24V 8A
Contact resistance	$\leq 0.03 \Omega$
Insulation resistance	$\geq 100M \Omega$ DC250V
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-40C° - +85C°
service life	5000cycles



5	圆针	1	黄铜棒	镀银
4	盖片	1	H62黄铜带(Y)	镀银
3	簧片	1	磷铜带	铜锡
2	屏蔽罩	1	H62黄铜带(Y)	黑
1	基座	1	PPA	黑
序号	名称	数量	材料	备注

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING		TITLE DC电源连接器C2. 5带屏蔽（弯插）		REV.	A
CHECK					
APPROVAL		PART NO. LAIL-DC24-D6. 5C2. 5-W		UNITS	mm
TOLERANCES ARE					
30-150	±0.35	ANGLE ±3°	DWG.NO.	Projection	
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				