








ROHS



RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



技术指标:

1. 材质

胶芯:LCP,UL94V-0; COLOR: BLACK

端子C2680

外壳:SPCC/C2680

2. 电镀说明

端子:接触区域镀金

焊锡区域镀: 雾锡100 u"Min

全部区域: 镍底 50 u" Min

外壳:表面镀镍100 u" Min

3. 电气性能:

绝缘阻抗(EIA-364-21):100 MΩ MIN.

AT 500V/DC FOR 1 MINUTE.

接触阻抗(EIA-364-06) 30 mΩ MAX.

耐电压(EIA-364-20) NO DISCHARGE,
FLASHOVER OR BREAKDOWN
AT 500 V/AC 1MINUTE.

4. 工作温度:-40℃ to +85℃

1	TMDS Data2+	11	TMDS Clock Shield
2	TMDS Data2 Shield	12	TMDS Clock-
3	TMDS Data2-	13	CEC
4	TMDS Data 1+	14	Reserved (N.C)
5	TMDS Data 1 Shied	15	SCL
6	TMDS Data 1-	16	SDA
7	TMDS Data 0+	17	DDC/CEC Ground
8	TMDS Data 0 Shield	18	+5V Power
9	TMDS Data 0-	19	Hot Plug Detect
10	TMDS Clock+		

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLEHDMI-A连接器19PIN母端弯插REV.A			
CHECK					
APPROVAL					
TOLERANCES ARE		PART NO.LAIL-HDMI-A01-A-WCUNITSmm			
30-150	±0.35	ANGLE ±3°	DWG.NO.		
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				