







ROHS



TF CARD PIN DEFINE			
PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)



WITHOUT CARD	OPEN	CD GND
INSERTING CARD	CLOSE	CD GND



—NOTES—

1.Electrical:

Contact resistance:50m ohms max.

Dielectric withstanding voltage:500V RMS.

Insulation resistance:1000M ohms min.

2.Mechanical:

MATE AND UNMATE FORCE:

MATE FORCE:4.5kg MAX

UNMATE FORCE:0.5kg MIN

Durability:1500cycles MIN.

3.Environment:

Operating Temperature:-25'to+85'.

4.FINISH:


TERMINAL: C5191,Ni UNDERPALTED OVERALL

G/F PALTED ON CONTACT AREA & SOLDER AREA

Shell: SUS201, Ni UNDERPLATED OVERALL.

G/F PALTED ON SOLDER AREA

HOUSING: LCP UL94V-0 ,BLACK



RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ± 0.05

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	MicroSD卡(TF卡)卡座T3.0(插拔式)	REV.	A	
30-150	±0.35	PART NO.	LAIL-TF06-T3.0-B	UNITS	mm	
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
ANGLE		DWG.NO.		Projection		
±3°						


ROHS

User Direction of Unreeling

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES

1. NUMBER OF CONNECTORS:SEE TABLE 2
2. LEAD TAPE LENGTH



COVER TAPE PEELING ANGLE:165°~180°
PEELING FORCE:20~130g

CARRIER TAPE

3.QUANTITY: 10REEL/CARTON

User Direction of Unreeling

DETAIL B

DETAIL B

4-TRIANGLE PARTITION

CARTON
345*345*310mm

TAPE ON

LABEL

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD					
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	MicroSD卡 (TF卡) 卡座T3.0 (插拔式)	REV.	A		
30-150	±0.35	PART NO.	LAIL-TF06-T3.0-B	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection			
±3°							