









MATERIALS

1. HOUSING : THERMOPLASTIC (UL 94V-0).
2. TERMINAL : COPPER ALLOY, PLATING SEE TABLE.
3. SHELL : SUS.

SPECIFICATION

1. CURRENT RATING : 0.5 A. MAX.
2. DIELECTRIC WITHSTANDING VOLTAGE : 500V AC R.M.S. FOR 1 MINUTE.
3. INSULATION RESISTANCE : 1000M Ω MIN.AT 500V DC.
4. CONTACT RESISTANCE : 100m Ω MAX.
5. OPERATING LIFE: 3000 CYCLES.
6. OPERATING TEMPERATURE : -40°C TO +85°C.
7. CIRCUIT DIAGRAM FOR CARD DETECT SWITCH


GND(PIN 10)
NORMAL.....SHORT
INSERTING CARD.....OPEN



PAD AREA

KEEP OUT AREA

Circuit Diagram for Detect Switch



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

TF CARD PIN DEFINE

PIN NO.	NAME	TYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)
9	SWA		

E	SW-B	1	STAINLESS STEEL	Ni/Au PLATING
D	SW-A	1	COPPER ALLOY	Ni/Au PLATING
C	SHELL-A	1	STAINLESS STEEL	Ni/Au PLATING
B	CONTACT	8	COPPER ALLOY	Gold Flash On Contact Area Tin plated on Solder tail All over Nickel Plated .
A	HOUSING	1	HIGH-TEMPERATURE PLASTIC UL94-V0	BLACK
NO	DESCRIPTION	QTY	MATERIAL	PLATING & COLOR

CUSTOMER DRAWING

深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO., LTD

DRAWING
CHECK

APPROVAL


TOLERANCES ARE

30-150	± 0.35	ANGLE $\pm 3^\circ$
10-30	± 0.2	
5-10	± 0.15	
0-5	± 0.1	


TITLE	SD存储卡卡座T1.3 (插拔式卡)	REV.	A
PART NO.	LAIL-TF07-T1.3-B	UNITS	mm
DWG.NO.		Projection	

ROHS

<图一>




COVER TAPE



放料方向

COVER TAPE




<图二>

20 EMPTY CARRIER TAPE

20 EMPTY CARRIER TAPE


48.4 REF.

COVER TAPE



LABEL


COVER TAPE PEELING FORCE:50gf~150gf



<TABLE 1> PACKAGING QUANTITY

QTY/REEL	REEL/CARTON	QTY/CARTON
1500	10	15000

<图三>



备注:

1. 按<图一>所示放置产品于Carrier tape中,每次放置1PCS产品,Carrier tape卷绕时,首端和尾端各需预留20PCS空卷。
2. Cover tape要盖Carrier tape首端需预留200mmMIN,后端需预留300mmMIN,两端都要盖大盖面。
3. 包装和包好,在Reel的每个分点贴上标签,以停止REEL展开,每Reel贴1PCS标签,如<图二>所示。
4. 包装数量见如<TABLE 1>所示。
5. 包装数量见如<图三>所示。
6. 封箱,在封好的纸箱侧面中间位置贴上出货标签。

COSTOMER DRAWING

DRAWING
CHECK
APPROVAL

TOLERANCES ARE

30-150	±0.35	ANGLE
10-30	±0.2	
5-10	±0.15	
0-5	±0.1	

LAILIAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO., LTD

TITLE	SD存储卡卡座T1.3 (插拔式卡)	REV.	A
PART NO.	LAIL-TF07-T1.3-B	UNITS	mm
DWG.NO.		Projection	