








ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



PCB.WELDING DRAWING (TOLERANCE:±0.05)



Main technical performance	
Rated electrical load	DC 24V 2.5A
Contact resistance	≤0.03Ω
Insulation resistance	≥100MΩ DC250V
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-20C°~+70C°
service life	5000cycles

4	TERMINAL	1	BRASS	MB:CuSn PLATED	
3	HOUSING	1	PPA	BLACK	
2	TIP SPRING	1	PHOSPHOR BRONZE	MB:CuSn PLATED	
1	CENTER PIN	1	BRASS	MB:CuSn PLATED	
LTR	PART NAME	QTY	MATERIAL	REMARK	
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLE DC电源连接器C2.0带屏蔽（弯插） REV. A			
CHECK					
APPROVAL					
TOLERANCES ARE					
30-150	±0.35	PART NO.	LAIL-DC24-D6.1C2.0-W	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO.		Projection	
±3°					