





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE






SIM pin assignment	
PIN#	Name
C1	VCC 电压
C2	RST 重置
C3	CLK 时钟
C5	GND 接地
C6	VPP 电压
C7	I/O 输入输出



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司	
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD	
CHECK			
APPROVAL			
TOLERANCES ARE		TITLE	SIM卡卡座T1.85 (自弹式卡)
30-150	± 0.35	PART NO.	LAIL-SIM01-T1.85-T
10-30	± 0.2	UNITS	mm
5-10	± 0.15	DWG.NO.	
0-5	± 0.1	Projection	

ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

PULL OUT DIRECTION

NOTE:

- 1.10 SPROCKET HOLE PITCH CUMULATEVE TOLERANCE±0.2
- 2.CARRIER CAMBER IS WITHIN 1 MM IN 250MM.
- 3.MATERIAL:BLACK CONDUCTIVE POLYSTYRENE ALLOY 100% RECYCLABLE.
- 4.ALL DIMENSIONS MEET EIA-481-B REQUIREMENTS.
- 5.THICKNESS:0.3±0.05MM.
- 6.COMPONENT LOAD PER 13"REEL:700 PCS.
- 7.A BOX OF 3 VOLUMES, 2100PCS
- 8.纸箱规格: 345*345*315,纸箱重为300G
- 9.重量: 每盘700PCS重1500G,每PCS重1.3G/PCS

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司					
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD					
CHECK								
APPROVAL								
TOLERANCES ARE			TITLE		SIM卡卡座T1.85（自弹式卡）		REV.	A
30-150	±0.35	ANGLE	PART NO.		LAIL-SIM01-T1.85-T		UNITS	mm
10-30	±0.2							
5-10	±0.15							
0-5	±0.1							
			DWG.NO.				Projection	