






2P结构样式

PCB LAYOUT
适用线路板 (厚度1.6mm)

技术指标(Technical Index):

- 1.额定电流(Rated current):2.0A AC,DC.
- 2.额定电压(Rated voltage):250V DC/AC (rms).
- 3.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 4.耐压值 (Dielectricwithstanding voltage): 800V AC/minute.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.适用线规(Apply to gauge):AWG#28~#24
- 7.工作温度(Temperature range):-25°C~+85° C.

材质 (Material)

Housing: LCP UL94 V-0 本色

Terminal:Copper Alloy/Tin Plating

Cap: LCP UL94 V-0 本色

CKT	PART.NO	A	B
2*2	W-2008N04P-0000	2.0	6.0
2*3	W-2008N06P-0000	4.0	8.0
2*4	W-2008N08P-0000	6.0	10.0
2*5	W-2008N10P-0000	8.0	12.0
2*6	W-2008N12P-0000	10.0	14.0
2*7	W-2008N14P-0000	12.0	16.0
2*8	W-2008N16P-0000	14.0	18.0
2*9	W-2008N18P-0000	16.0	20.0
2*10	W-2008N20P-0000	18.0	22.0
2*11	W-2008N22P-0000	20.0	24.0
2*12	W-2008N24P-0000	22.0	26.0
2*13	W-2008N26P-0000	24.0	28.0
2*14	W-2008N28P-0000	26.0	30.0
2*15	W-2008N30P-0000	28.0	32.0
2*16	W-2008N32P-0000	30.0	34.0
2*18	W-2008N36P-0000	34.0	38.0
2*20	W-2008N40P-0000	38.0	42.0

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO.,LTD			
CHECKED:	DATE:	TITLE: 2008SMT-2*XP 立贴 (PHD 双排)			
DRAWN: LYF	DATE: 2024-5-26	PART. NO.	W-2008NXXP-0000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-2008-0019		REV. A WD01

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05