






ROHS



Main technical performance	
Rated electrical load	DC 24V 3A
Contact resistance	$\leq 0.03 \Omega$
Insulation resistance	$\geq 100M\Omega$ DC250V
Pressure resistance	AC 500V 1min
Insertion force	3-20N
Operating temperature range	-20C°~+70C°
service life	5000cycles

4	TERMINAL	1	BRASS	MB:CuSn PLATED
3	HOUSING	1	PBT	BLACK
2	TIP SPRING	1	PHOSPHOR BRONZE	MB:CuSn PLATED
1	CENTER PIN	1	BRASS	MB:CuSn PLATED
LTR	PART NAME	QTY	MATERIAL	REMARK
CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
DRAWING		TITLE DC电源连接器C2.0带屏蔽（弯插）REV. A		
CHECK				
APPROVAL				
TOLERANCES ARE				
30-150	±0.35	PART NO. LAIL-DC24-D5.9C2.0-W	UNITS	mm
10-30	±0.2			
5-10	±0.15			
0-5	±0.1			
ANGLE		DWG.NO.	Projection	
±3°				