



ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



MATERIAL:




INSULATOR: HIGH TEMPERATURE THERMOPLASTIC, UL 94V-0
CONTACT: COPPER ALLOY
SHELL: SUS

PLATING:

CONTACT: PLATED 50U" NI OVER ALL CONTACT AU 1U
SHELL: PLATED 50U" NI OVERALL
PLATED 1U" AU SELECTIVE CONTACT AREA

ELECTRICAL:

CURRENT RATING: 0.5MA
VOLTAGE RATING: 5V AC/DC
AMBIENT TEMPERATURE RANGE: -40℃ ~ +85℃
STORAGE TEMPERATURE RANGE: -40℃ ~ +85℃
AMBIENT HUMIDITY RANGE: 95% R.H. MAX.
CONTACT RESISTANCE: 100M MAX.Ω
INSULATION RESISTANCE: 1000M MIN./500VDCΩ
REFLOW PEAK TEMP: 260℃
MATING CYCLES: 5000MIN INSERTIONS
Salt spray time: 24H



MICRO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A

COSTOMER DRAWING



LAILIAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO., LTD

DRAWING	CHECK	APPROVAL
TOLERANCES ARE		
30-150	±0.35	ANGLE ±3°
10-30	±0.2	
5-10	±0.15	
0-5	±0.1	

TITLE	SIM卡卡座T1.35 (自弹式卡)	REV.	A
PART NO.	LAIL-SIM03-T1.35-T	UNITS	mm
DWG.NO.		Projection	

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



MATERIAL:





INSULATOR: HIGH TEMPERATURE THERMOPLASTIC, UL 94V-0
CONTACT: COPPER ALLOY
SHELL: SUS

PLATING:

CONTACT: PLATED 50U" NI OVER ALL CONTACT AU 1U
SHELL: PLATED 50U" NI OVERALL
PLATED 1U" AU SELECTIVE CONTACT AREA

ELECTRICAL:

CURRENT RATING: 0.5MA
VOLTAGE RATING: 5V AC/DC
AMBIENT TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
STORAGE TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
AMBIENT HUMIDITY RANGE: 95% R.H. MAX.
CONTACT RESISTANCE: 100M MAX.^②
INSULATION RESISTANCE: 1000M MIN./500VDC^②
REFLOW PEAK TEMP: 260 $^{\circ}\text{C}$
MATING CYCLES: 5000MIN INSERTIONS
Salt spray time: 24H



MICRO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	SIM卡卡座T1.35 (自弹式卡)	REV.	A
30-150	±0.35	PART NO.	LAIL-SIM03-T1.35-T	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO.		Projection	
±3°					