









ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



Main technical performance	
Rated electrical load	DC 24V 3A
Temperature	-30℃~+70℃
Insulation resistance	≥100MΩ
Contact Resistance	≤0.3Ω
Pressure resistance	AC500V (50Hz)/min
Insertion force	3-20N
service life	5000cycles



6	圆针	1	黄铜棒	亮锡
5	平片	1	H62黄铜带(Y)T=0.35	亮锡
4	弯片	1	H62黄铜带(Y)T=0.3	亮锡
3	簧片	1	磷铜带T=0.25	亮锡
2	后盖	1	PA9T	黑色
1	基座	1	PA9T	黑色
序号	名称	数量	材料	备注
CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司	
DRAWING CHECK			SHENZHEN LAILIAN ELECTRONICS CO., LTD	
APPROVAL			TITLE	DC电源连接器C2.0 (SMT贴片)
TOLERANCES ARE			REV.	A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-DC24-D6.5C2.0-SMT
10-30	±0.2		UNITS	mm
5-10	±0.15		DWG.NO.	
0-5	±0.1		Projection	