







ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

Specification:

1. ELECTRICAL CHARACTERISTICS
 - 1-1. CONTACT RESISTANCE: 80 milliohms MAX.
 - 1-2. INSULATION RESISTANCE: 1,000 Megohms MIN.
 - 1-3. DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE.
2. MECHANICAL CHARACTERISTICS
 - 2-1. DURABILITY: 5,000 CYCLES
3. RoHS 2002/95/EC COMPLIANT.



RECOMMEND PCB LAYOUT
(TOLERANCE:±0.05)




Pin No.	Pin assignment
PIN1	DAT2
PIN2	CD/DAT3
PIN3	CMD
PIN4	VDD
G1	SWITCH
PIN5	CLK
PIN6	VSS
PIN7	DAT0
PIN8	DAT1

C	SHELL	1	STAINLESS STEEL 0.15t	NI PLATING
B	CONTACT	9	COPPER ALLOY 0.15t	Gold Flash On Contact Area Tin plated on Solder tail All over Nickel Plated
A	HOUSING	1	HIGH-TEMPERATURE PLASTIC UL94-V0	BLACK
NO	DESCRIPTION	QTY	MATERIAL	PLATING & COLOR

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	MicroSD卡 (TF卡) 卡座 (插拔式)	REV.	A
30-150	±0.35	PART NO.	LAIL-TF04-T1. 7-B	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1	DWG.NO.	Projection 		


ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE





NO. 1

NO. 2



纸箱规格:340*340*300

NO. 4



NO. 3

1. 材质要求:
- 1.1 纸箱的材质为A=B;外形尺寸为34*34*30;
 - 1.2 卷盘的材质为PVC,卷盘的外形尺寸为 $\phi 330 \times 30.4$;
 - 1.3 卷带的材质为PVC,卷带的外形尺寸为24400*24.00*2.4mm;
2. 包装方式:
- 2.1 将卷带放入包装机后,前空20PCS,后放产品2500PCS,再后空28PCS.
 - 2.2 将包装好的产品从包装机上取下并包装好;
 - 2.3 把累叠好的11盘叠放入纸箱中共计27.5Kset;
 - 2.4 把包装好的成品打包封箱,并在纸箱外贴上标签

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	MicroSD卡(TF卡)卡座(插拔式)	REV.	A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-TF04-T1.7-B	UNITS	mm
10-30	±0.2		DWG.NO.		Projection	
5-10	±0.15					
0-5	±0.1					