





ROHS



PRPDUCT



RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)
RECOMMENDED MATAL MASK T=0.12mm

- Legend for PCB layout:
- SMT SOLDER AREA
 - NO PATTERN AND VIA HOLE IN HTIS AREA

NOTES:

1.MATERIAL:

HOUSING: High Temperature Thermoplastic

Terminal:Copper Alloy

Shell: Stainless Steel

2.PLATING:

Terminal:30u" Ni UNDERPLATED OVERALL

G/F PLATED ON CONTACT AREA AND SOLDER AREA

Shell:30u" Ni UNDERPLATED OVERALL

G/F PLATED ON CONTACT AREA AND SOLDER AREA

3.technical speciality:

RATED VOLTAGE: 30V AC MAX.


CURRENT RATING: 0.5A MAX.

INSULATION RESISTANCE:1000MΩMIN

CONTACT REISTANCE:100mΩMAX

WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTES

OPERATING TEMPERATURE: -40℃~+85℃Humidity 80% R.H MAX



COSTOMER DRAWING

DRAWING
CHECK
APPROVAL

TOLERANCES ARE

30-150	±0.35
10-30	±0.2
5-10	±0.15
0-5	±0.1

ANGLE
±3°

LAILAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO., LTD


TITLE	SIM卡卡座T1.37 (自弹式)	REV.	A
PART NO.	LAIL-SIM06-T1.37-T	UNITS	mm
DWG.NO.		Projection	

ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES

1. NUMBER OF CONNECTORS:1500PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY:15000PCS/CARTON
4. WEIGHT :
 - 3.1 NET WEIGHT : Kg
 - 3.2 GROSS WEIGHT : Kg



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	SIM卡卡座T1.37（自弹式）	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-SIM06-T1.37-T	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		±3°	DWG.NO.			