




REV.	ECN NO.	DESCRIPTION	DRAW	DATE



规格:

- 1.插入力:44.1N MAX.
- 2.拔出力:9.8~25N
- 3.耐久性:10000 CYCLES MIN.
- 4.额定电流:0.5A
- 5.额定电压:40V MAX
- 6.耐电压:500V AC MIN.(UNMATED)
300V AC MIN.(MATED)
- 7.接触阻抗:30m Ω MAX.
- 8.绝缘电阻:100M Ω MIN(UNMATED)
10M Ω MIN(MATED)
- 9.工作温度:-40℃ TO +85℃
- 10.所用材质符合 RoHS要求

1	TMDS Data2+	11	TMDS Clock Shield
2	TMDS Data2 Shield	12	TMDS Clock-
3	TMDS Data2-	13	CEC
4	TMDS Data1+	14	Reserved (N.C.on device)
5	TMDS Data1 Shield	15	SCL
6	TMDS Data1-	16	SDA
7	TMDS Data0+	17	DDC/CEC Ground
8	TMDS Data0 Shield	18	+5V Power
9	TMDS Data0-	19	Hot Plug Detect
10	TMDS Clock+		

COSTOMTER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD		
DRAWING			TITLE HDMI-A连接器19PIN母端侧插 REV. A		
CHECK					
APPROVAL					
TOLERANCES ARE			PART NO. LAIL-HDMI-A02-A-CC	UNITS mm	DWG.NO. Projection
30-150	±0.35	ANGLE ±3°			
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				