

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES:

1. MATERIAL:

1-1.Insulator: High Temperature Thermoplastic,
UL94V-0; Color Black.

1-2.Terminal: Copper Alloy.

1-3.Shell: Stainless Steel.

2. PLATING:

2-1.Contact: Plated 50u" Ni Overall Contact, Au 1u",

2-2.Shell: Plated 50u" Ni Overall,PAD Au 1u"

3. SPECIALITY:

3-1.Current Rating :0.5mA AC/DC max.

3-2.Voltage Rating :125V AC/DC

3-3.Ambient Temperature Range :-20°C~+60°C

3-4.Storage Temperature Range :-40°C~+70°C

3-5.Ambient Humidity Range :95% R.H. Max.







3-6.Contact Resistance:100mΩ max.

3-7.Insulation Resistance:1000MΩ min./500VDC

3-8.Mating Cycles:10,000 Insertions

3-9.Reflow peak temp.:260°C ±5°C, 3~5 S

3-10.Mating Cycles:3,000 Insertions Min




SIM pin assignment	
PIN#	Name
C1	VCC 供电电压
C2	RST 重置
C3	CLK 时钟
C5	GND 接地
C6	VPP 程序电压
C7	I/O 输入输出

COSTOMTER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	SIM卡卡座T1.35（插拔式）	REV.	A	
30-150	±0.35	PART NO.	LAIL-SIM07-T1.35-B	UNITS	mm	
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
ANGLE		DWG.NO.		Projection		
±3°						


ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE




NOTES

1. NUMBER OF CONNECTORS: 1800PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 18000PCS/CARTON



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	SIM卡卡座T1.35（插拔式）	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-SIM07-T1.35-B	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			DWG.NO.		Projection	