

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Materials and Electroplating




- ①. Plastic body: PA66
②. Clip: Copper, nickel plated
③. Square box: Copper, nickel plated
④. Plastic cover plate: PA66
⑤. Screw: M2.0, iron, galvanized, straight groove

Electrical performance

Rated voltage: 300V
Rated current: 8A
Contact resistance: 20m Ω (Max)
Insulation resistance: 500M Ω \ DC500V
Voltage endurance: AC1500V \ 1Min
Using wire diameter: 28-16AWG 1.5mm²

mechanical properties

Temperature range: -40 $^{\circ}\text{C}$ ~ +105 $^{\circ}\text{C}$
Instantaneous temperature: +250 $^{\circ}\text{C}$ for 5 econds
Torque: 0.2Nm (1.77Lbin)
Stripping length: 6-7mm



2	方盒	铜	镀镍	
1	基座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	接线端子
料 号 PART NO	HC-JXDZKM-3.81-5P

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1



公差等级	公差
2-6P	±0.10 ±0.20
7-12P	±0.20 ±0.30
13-18P	±0.25 ±0.40
19-24P	±0.30 ±0.50

X.X ±0.35
X.XX ±0.25
X.XXX ±0.15单 位
UNIT

MM

制 图
DRAW

AhYe

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

版 本
REV

A

批 准
APPROVE

赵亮亮

