

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

Materials and Electroplating

- ①. Plastic body: PA66
- ②. Clip: Copper, nickel plated
- ③. Square box: Copper, nickel plated
- ④. Plastic cover plate: PA66
- ⑤. Screw: M2.0, iron, galvanized, straight groove

Electrical performance

Rated voltage: 300V

Rated current: 8A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1Min

Using wire diameter: 28-16AWG 1.5mm²





mechanical properties

Temperature range: -40 °C~+105 °C

Instantaneous temperature: +250 °C for 5 econds

Torque: 0.2Nm (1.77Lbin)

Stripping length: 6-7mm



2	方盒	铜	镀镍	
1	底座	PA66	绿色	
序 号	品 名	材 质	电镀/颜色	备 注




深圳市虹成电子有限公司

品 名 TITLE	接线端子
料 号 PART NO	HC-JXDZK-3.81-5P

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 列
SCALE

1:1



公差参数	公差
2-6P	±0.10 ±0.20
7-12P	±0.20 ±0.30
13-18P	±0.25 ±0.40
19-24P	±0.30 ±0.50

X. X ±0.35
X. XX ±0.25
X. XXX ±0.15单 位
UNIT

MM

制 图
DRAW

AhYe

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

版 本
REV

A

批 准
APPROVE

赵亮亮

