





标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PCB LAYOUT

Materials and Electroplating

- ①. Plastic body: PA66
- ②. Solder pin: copper, Nickel tin plating
- ③. Nut: Copper, Nickel Plated

Electrical performance

Rated voltage: 300V

Rated current: 8A

Contact resistance: $20m \Omega$ (Max)Insulation resistance: $500M \Omega$ \ DC500V

Voltage endurance: AC1500V \ 1Min

mechanical properties

Temperature range: $-40^{\circ}C \sim +105^{\circ}C$ Instantaneous temperature: $+250^{\circ}C$, 5 seconds

2	插针	铜	镀镍锡	
1	底座	PA66	绿色	
序号	品名	材质	电镀/颜色	备注

	品名 TITLE		接线端子	
	料号 PART NO		HC-JXDZVM-3.81-5P	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1	
单位 UNIT		MM	制图 DRAW	AhYe
张数 PART NO		1 OF 1	审核 CHECKED	夏操云
版本 REV		A	批准 APPROVE	赵亮亮

公差范围	公差范围	公差范围
2-6P	± 0.10	± 0.20
7-12P	± 0.20	± 0.30
13-18P	± 0.25	± 0.40
19-24P	± 0.30	± 0.50

X.X ± 0.35
X.XX ± 0.25
X.XXX ± 0.15 制图
DRAW审核
CHECKED批准
APPROVE

AhYe

夏操云

赵亮亮

