






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE



PCB LAYOUT

Materials and Electroplating

- ①. Plastic body: PA66
- ②. Solder pin: copper, nickel tin plated
- ③. Nut: Copper, Nickel Plated

Electrical performance

Rated voltage: 300V

Rated current: 15A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1min

mechanical properties

Temperature range: -40 ℃~+105 ℃

Instantaneous temperature: +250 ℃, 5 seconds

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名	接线端子																		
			TITLE																			
			料 号	HC-JXDZRM-5.08-2P																		
			PART NO																			
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列	1:1																			
		单 位	MM	制 图	AhYe																	
		UNIT		DRAW																		
<table border="1"><tr><th colspan="2">公差参数</th><th rowspan="2">未注明公差:</th></tr><tr><th>PIN NO</th><th></th></tr><tr><td>2-6P</td><td>±0.10</td><td>±0.15</td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.35</td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td></tr></table>		公差参数		未注明公差:	PIN NO		2-6P	±0.10	±0.15	7-12P	±0.20	±0.30	13-18P	±0.25	±0.35	19-24P	±0.30	±0.50	张 数	1 OF 1	审 核	夏操云
		公差参数			未注明公差:																	
		PIN NO																				
2-6P	±0.10	±0.15																				
7-12P	±0.20	±0.30																				
13-18P	±0.25	±0.35																				
19-24P	±0.30	±0.50																				
		PART NO		CHECKED																		
		版 本	A	批 准	赵亮亮																	
		REV		APPROVE																		

