

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Materials and Electroplating

- ①. Plastic body: PA66
②. Solder pin: copper, Nickel tin plating

Electrical performance




Rated voltage: 300V

Rated current: 8A

Contact resistance: 20m Ω (Max)Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1Min

mechanical properties

Temperature range: -40 $^{\circ}\text{C}$ ~+105 $^{\circ}\text{C}$ Instantaneous temperature: +250 $^{\circ}\text{C}$, 5 seconds

PCB LAYOUT

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名 TITLE	接线端子
料号 PART NO	HC-JXDZVC-3.81-6P

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1



公差参数	公差	公差
2-6P	±0.10	±0.20
7-12P	±0.20	±0.30
13-18P	±0.25	±0.40
19-24P	±0.30	±0.50

张数 PART NO	±0.35
版 本 REV	±0.25
	±0.15

单位 UNIT	MM
张数 PART NO	1 OF 1
版 本 REV	A

制图 DRAW	AhYe
审核 CHECKED	夏操云
批准 APPROVE	赵亮亮

