






标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PCB LAYOUT

Materials and Electroplating

①. Plastic body: PA66

②. Solder pin: copper, nickel tin plated

Electrical performance

Rated voltage: 300V

Rated current: 15A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1Min

mechanical properties

Temperature range: -40 °C~+105 °C

Instantaneous temperature: +250 °C, 5 seconds

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	接线端子
料号 PART NO	HC-JXDZV-5.08-12P

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1

公差参数	公差	公差
2-6P	±0.10	±0.20
7-12P	±0.20	±0.30
13-18P	±0.25	±0.40
19-24P	±0.30	±0.50

X. xxx ±0.15
X. xx ±0.25
X. x ±0.35单 位
UNIT

MM

制 图
DRAW

AhYe

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

版 本
REV

A

批 准
APPROVE

赵亮亮

