





标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Materials and Electroplating

- ①. Screw: M2.5, iron, galvanized, straight groove
②. Plastic body: PA66
③. Clip: Copper, nickel plated
④. Square box: iron, nickel plated
⑤. Plastic cover plate: PA66
Electrical performance
Rated voltage: 300V
Rated current: 15A
Contact resistance: 20m Ω (Max)
Insulation resistance: 500M Ω/DC500V
Voltage endurance: AC1500V/1Min
Wire diameter used: 28-12AWG
mechanical properties
Temperature range: -40 °C~+105 °C
Instantaneous temperature: +250 °C for 5 seconds
Torque: 0.4Nm (3.6 Ib. in)
Stripping length: 7-8mm



2	方盒	铁	镀镍	
1	底座	PA66	绿色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品 名		接线端子																				
			料 号		HC-JXDZK-5.08-15P-A																				
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列	1:1																					
<table border="1"><thead><tr><th colspan="3">公差参数</th></tr><tr><th>公差</th><th>公差</th><th>公差</th></tr></thead><tbody><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td><td rowspan="3">X. xxx ±0.15 X. xx ±0.25 X. x ±0.35</td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td></tr></tbody></table>			公差参数			公差	公差	公差	2-6P	±0.10	±0.20	X. xxx ±0.15 X. xx ±0.25 X. x ±0.35	7-12P	±0.20	±0.30	13-18P	±0.25	±0.40	19-24P	±0.30	±0.50	单 位	MM	制 图	AhYe
			公差参数																						
			公差	公差	公差																				
2-6P	±0.10	±0.20	X. xxx ±0.15 X. xx ±0.25 X. x ±0.35																						
7-12P	±0.20	±0.30																							
13-18P	±0.25	±0.40																							
19-24P	±0.30	±0.50																							
			张 数	1 OF 1	审 核	夏操云																			
			版 本	A	批 准	赵亮亮																			
					APPROVE																				