







		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	





SECTION A-A


技术指标:

适用线路板(PCB LAYOUT)

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: $50\text{V}, \text{AC}/\text{DC}$ (等效)。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500\text{M}\Omega$ 。




Applicable Flat Cable



Part No	Pin	A	B	C
FPC-010-S2-FCA	2	1.00	3.10	6.90
FPC-010-S3-FCA	3	2.00	4.10	7.90
FPC-010-S4-FCA	4	3.00	5.10	8.90
FPC-010-S5-FCA	5	4.00	6.10	9.90
FPC-010-S6-FCA	6	5.00	7.10	10.90
FPC-010-S7-FCA	7	6.00	8.10	11.90
FPC-010-S8-FCA	8	7.00	9.10	12.90
FPC-010-S9-FCA	9	8.00	10.10	13.90
FPC-010-S10-FCA	10	9.00	11.10	14.90
.....		...		
FPC-010-S32-FCA	32	(32-1)*1.0	(32+1)*1.0+0.10	(32+5)*1.0-0.10

序号	品名	材质
1	0.5首飾貼芯(H2.0)	LCP UL94V-0 本色
2	0.5首飾銅子(H2.0)	銅合金/表面鍍鎳
3	0.5首飾后蓋(H2.0)	LCP UL94V-0 黑色
4	0.5首飾母片(H2.0)	銅合金/表面鍍鎳



GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. .x ±0.30 .xx ±0.20 .xxx ±0.05 GENERAL ANGLE: .x° ±5° .XX° ±2° .XXX° ±1°		TITLE: 1.0 Pitch 前翻脚式下接 (H=2.0)						
		DWG. NO.: FPC-010-SX-FCA			CHECKED: MAX			
		PART NO.: FPC-010-SX-FCA			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	