

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

Materials and Electroplating

- ①. Plastic body: PA66
- ②. Clip: Copper, nickel plated
- ③. Square box: Copper, nickel plated
- ④. Plastic cover plate: PA66
- ⑤. Screw: M2.0, iron, galvanized, straight groove

Electrical performance

Rated voltage: 300V

Rated current: 8A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1Min

Using wire diameter: 28-16AWG 1.5mm²





mechanical properties

Temperature range: -40 °C~+105 °C

Instantaneous temperature: +250 °C for 5 econds

Torque: 0.2Nm (1.77Lbin)

Stripping length: 6-7mm



2	方盒	铜	镀镍	
1	底座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名		接线端子																			
			料 号		HC-JXDZK-3.81-4P																			
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列	1:1																				
<table border="1"><tr><th colspan="3">公差参数</th></tr><tr><th>PinNo</th><th>DimP</th><th>DimL</th></tr><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td></tr></table>			公差参数			PinNo	DimP	DimL	2-6P	±0.10	±0.20	7-12P	±0.20	±0.30	13-18P	±0.25	±0.40	19-24P	±0.30	±0.50	单 位	MM	制 图	AhYe
			公差参数																					
			PinNo	DimP	DimL																			
			2-6P	±0.10	±0.20																			
			7-12P	±0.20	±0.30																			
13-18P	±0.25	±0.40																						
19-24P	±0.30	±0.50																						
			张 数	1 OF 1	审 核	夏操云																		
			PART NO		CHECKED																			
			版 本	A	批 准	赵亮亮																		
			REV		APPROVE																			