

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

A

B

C

D

E

F

G

A

B




C

D

E

F

G



PCB LAYOUT

Materials and Electroplating

- ①. Plastic body: PA66,
- ②. Solder pin: copper, Nickel tin plating

Electrical performance

Rated voltage: 300V

Rated current: 8A

Contact resistance: $20\text{m} \Omega$ (Max)Insulation resistance: $500\text{M} \Omega$ \ DC500V

Voltage endurance: AC1500V \ 1Min

mechanical properties

Temperature range: $-40^\circ\text{C} \sim +105^\circ\text{C}$ Instantaneous temperature: $+250^\circ\text{C}$, 5 seconds

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名 TITLE	接线端子
料号 PART NO	HC-JXDZVC-3.5-16P

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1



公差参数

尺寸	公差	公差
2-6P	± 0.10	± 0.20
7-12P	± 0.20	± 0.30
13-18P	± 0.25	± 0.40
19-24P	± 0.30	± 0.50

X.X	± 0.35
X.XX	± 0.25
X.XXX	± 0.15

单位
UNIT

MM

制 图
DRAW

AhYe

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

版 本
REV

A

批 准
APPROVE

赵亮亮

