






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE



PCB LAYOUT

Materials and Electroplating

- ①. Plastic body: PA66
- ②. Solder pin: copper, nickel tin plated
- ③. Nut: Copper, Nickel Plated

Electrical performance

Rated voltage: 300V

Rated current: 15A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1min

mechanical properties

Temperature range: -40 ℃~+105 ℃

Instantaneous temperature: +250 ℃, 5 seconds

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	品 名 TITLE		接线端子	
料 号 PART NO		单 位 UNIT	MM	制 图 DRAW		AhYe	
张 数 PART NO		1 OF 1		审 核 CHECKED		夏操云	
版 本 REV		A		批 准 APPROVE		赵亮亮	

公差参数	公差	公差	公差
2-6P	±0.10	±0.20	
7-12P	±0.20	±0.30	
13-18P	±0.25	±0.40	
19-24P	±0.30	±0.50	

未注明公差:	
X. xxx	±0.15
X. xx	±0.25
X. x	±0.35

