







PC Board Layout
Component Side Shown

YELLOW
9 ————> 10 L

GREEN
11 ————> 12 R

说明:

1. 材质:

胶芯: PBT, UL94V-0; COLOR; BLACK

端子: C5191

外壳: C2680

2. 电镀说明:

端子: 镍底镀金G.F

外壳: 表面镀镍

3. 性能说明:

1) 电压: 150V AC RMS.

2) 额定电流: 1.5A.

3) 接触电阻: 40mΩ Max.

4) 绝缘电阻: 500MΩ MIN.

5) 绝缘耐压: 1000V AC.

6) 工作温度: -40° C TO +80° C.

7) 耐久性: 500 Mating Cycles MIN.

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: RJ45-10P/8C 59A TAB-Down H=21.35 弯插 带屏蔽 带灯 带弹片			
DRAWN: HCY	DATE: 2019-07-20	PART. NO.	R-RJ45R08P-C007		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0145	REV.	A HY04