






标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PCB LAYOUT

Materials and Electroplating

- ①. Plastic body: PA66
- ②. Solder pin: copper, nickel tin plated
- ③. Nut: Copper, Nickel Plated

Electrical performance

Rated voltage: 300V

Rated current: 15A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1min

mechanical properties

Temperature range: -40 ℃~+105 ℃

Instantaneous temperature: +250 ℃, 5 seconds

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	接线端子
料 号 PART NO	HC-JXDZRM-5.08-4P

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1

公差参数	公差	公差	公差
2-6P	±0.10	±0.20	
7-12P	±0.20	±0.30	
13-18P	±0.25	±0.40	
19-24P	±0.30	±0.50	

未注明公差:
X. xxx ±0.15
X. xx ±0.25
X. x ±0.35单 位
UNIT
张 数
PART NOMM
1 OF 1
A制 图
DRAW
审 核
CHECKED
批 准
APPROVEAhYe
夏操云
赵亮亮