

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Materials and Electroplating

- ①. Plastic body: PA66
②. Solder pin: copper, Nickel tin plating
③. Nut: Copper, Nickel Plated

Electrical performance





Rated voltage: 300V

Rated current: 8A

Contact resistance: 20m Ω (Max)Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1Min

mechanical properties

Temperature range: -40 $^{\circ}\text{C}$ ~+105 $^{\circ}\text{C}$ Instantaneous temperature: +250 $^{\circ}\text{C}$, 5 seconds

PCB LAYOUT

2	插针	铜	镀镍锡	
1	底座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	接线端子
料 号 PART NO	HC-JXDZRM-3.81-5P

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1

制 图
DRAW

AhYe

夏操云

审核

批准

赵亮亮

公差参数	公差	公差	公差
2-6P	±0.10	±0.20	
7-12P	±0.20	±0.30	
13-18P	±0.25	±0.40	
19-24P	±0.30	±0.50	

X.X ±0.35

X.XX ±0.25

X.XXX ±0.15

单 位
UNIT

MM

张 数
PART NO

1 OF 1

版 本
REV

A

制 图
DRAW

审核

批准

赵亮亮

夏操云

赵亮亮