

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

A

B

C

D

E

F

G

A

B






C

D

E

F

G



PCB LAYOUT

Materials and Electroplating

①. Plastic body: PA66

②. Solder pin: copper, nickel tin plated

Electrical performance

Rated voltage: 300V

Rated current: 15A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1Min

mechanical properties

Temperature range: -40 °C~+105 °C

Instantaneous temperature: +250 °C, 5 seconds

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品 名		接线端子																			
			料 号		HC-JXDZRC-5.08-4P																			
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列	1 : 1																				
<table border="1" data-bbox="1415 1345 1525 1399"><tr><th colspan="3">公差参数</th></tr><tr><th>公差</th><th>DinP</th><th>DinL</th></tr><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td></tr></table>			公差参数			公差	DinP	DinL	2-6P	±0.10	±0.20	7-12P	±0.20	±0.30	13-18P	±0.25	±0.40	19-24P	±0.30	±0.50	单 位	MM	制 图	AhYe
			公差参数																					
公差	DinP	DinL																						
2-6P	±0.10	±0.20																						
7-12P	±0.20	±0.30																						
13-18P	±0.25	±0.40																						
19-24P	±0.30	±0.50																						
			张 数	1 OF 1	审 核																			
			PART NO		CHECKED		夏操云																	
			版 本	A	批 准	赵亮亮																		
			REV		APPROVE																			