





标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Materials and Electroplating

- ①. Screw: M2.5, iron, galvanized, straight groove
②. Plastic body: PA66
③. Clip: Copper, nickel plated
④. Square box: iron, nickel plated
⑤. Plastic cover plate: PA66
Electrical performance
Rated voltage: 300V
Rated current: 15A
Contact resistance: 20m Ω (Max)
Insulation resistance: 500M Ω/DC500V
Voltage endurance: AC1500V/1Min
Wire diameter used: 28-12AWG
mechanical properties
Temperature range: -40 °C~+105 °C
Instantaneous temperature: +250 °C for 5 seconds
Torque: 0.4Nm (3.6 Ib. in)
Stripping length: 7-8mm



2	方盒	铁	镀镍	
1	底座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名	接线端子	
			TITLE		
			料 号	HC-JXDZK-5.08-7P-A	
			PART NO		
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 例	1 : 1	
			SCALE		
			单 位	MM	制 图
			UNIT		DRAW
			张 数	1 OF 1	AhYe
			PART NO	审 核	
				CHECKED	
			版 本	批 准	
			REV	APPROVE	