






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE



PCB LAYOUT

Materials and Electroplating

- ①. Plastic body: PA66
- ②. Solder pin: copper, nickel tin plated
- ③. Nut: Copper, Nickel Plated

Electrical performance

Rated voltage: 300V

Rated current: 15A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1min

mechanical properties

Temperature range: -40 ℃~+105 ℃

Instantaneous temperature: +250 ℃, 5 seconds

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名		接线端子																			
			TITLE																					
			料 号		HC-JXDZRM-5.08-16P																			
			PART NO																					
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列 SCALE		1:1																			
																								
<table border="1"><thead><tr><th colspan="3">公差参数</th></tr><tr><th>尺寸</th><th>公差</th><th>公差</th></tr></thead><tbody><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td></tr></tbody></table>			公差参数			尺寸	公差	公差	2-6P	±0.10	±0.20	7-12P	±0.20	±0.30	13-18P	±0.25	±0.40	19-24P	±0.30	±0.50	单位 UNIT		MM	
公差参数																								
尺寸	公差	公差																						
2-6P	±0.10	±0.20																						
7-12P	±0.20	±0.30																						
13-18P	±0.25	±0.40																						
19-24P	±0.30	±0.50																						
未注明公差: X. xxx ±0.15 X. xx ±0.25 X. x ±0.35			张 数 PART NO		1 OF 1																			
			版本 REV		A																			
			制 图 DRAW		AhYe																			
			审 核 CHECKED		夏操云																			
			批 准 APPROVE		赵亮亮																			
																								

