





标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Materials and Electroplating

- ①. Screw: M2.5, iron, galvanized, straight groove
②. Plastic body: PA66
③. Clip: Copper, nickel plated
④. Square box: iron, nickel plated
⑤. Plastic cover plate: PA66
Electrical performance
Rated voltage: 300V
Rated current: 15A
Contact resistance: 20m Ω (Max)
Insulation resistance: 500M Ω/DC500V
Voltage endurance: AC1500V/1Min
Wire diameter used: 28-12AWG
mechanical properties
Temperature range: -40 °C~+105 °C
Instantaneous temperature: +250 °C for 5 seconds
Torque: 0.4Nm (3.6 Ib. in)
Stripping length: 7-8mm



2	方盒	铁	镀镍	
1	底座	PA66	绿色	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名 TITLE	接线端子
料号 PART NO	HC-JXDZK-5.08-3P-A

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1



公差参数	公差	公差
2-6P	±0.10	±0.20
7-12P	±0.20	±0.30
13-18P	±0.25	±0.40
19-24P	±0.30	±0.50

X. xxx ±0.15
X. xx ±0.25
X. x ±0.35单 位
UNIT

MM

制 图
DRAW

AhYe

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

版 本
REV

A

批 准
APPROVE

赵亮亮

