







技术指标(Technical Index):

- 额定电流(Rated current):2.0A AC,DC.
- 额定电压(Rated voltage):250V DC/AC (rms).
- 接触电阻(Contact resistance):≤20mΩ.
- 耐压值 (Dielectricwithstanding voltage): 800V AC/minute.
- 绝缘电阻(Insulation resistance):≥1000MΩ.
- 适用线规(Apply to gauge):AWG#28~#24
- 工作温度(Temperature range):-25°C~+85° C.


材质 (Material)

Housing: LCP UL94 V-0 本色


Terminal:Copper Alloy/Tin Plating




2P结构




3P结构



PCB LAYOUT



5P结构



4P结构

CKT	PART.NO	A	B
2*2	W-2006M04P-0000	2.0	6.0
2*3	W-2006M06P-0000	4.0	8.0
2*4	W-2006M08P-0000	6.0	10.0
2*5	W-2006M10P-0000	8.0	12.0
2*6	W-2006M12P-0000	10.0	14.0
2*7	W-2006M14P-0000	12.0	16.0
2*8	W-2006M16P-0000	14.0	18.0
2*9	W-2006M18P-0000	16.0	20.0
2*10	W-2006M20P-0000	18.0	22.0
2*11	W-2006M22P-0000	20.0	24.0
2*12	W-2006M24P-0000	22.0	26.0
2*13	W-2006M26P-0000	24.0	28.0
2*14	W-2006M28P-0000	26.0	30.0
2*15	W-2006M30P-0000	28.0	32.0
2*16	W-2006M32P-0000	30.0	34.0
2*18	W-2006M36P-0000	34.0	38.0
2*20	W-2006M40P-0000	38.0	42.0

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO., LTD			
CHECKED:	DATE:	TITLE: 2006SMT-2*XP 带扣 卧贴 (PHDC 双排)			
DRAWN: LYF	DATE: 2024-5-26	PART. NO.	W-2006MXXP-0000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-2006-0006	REV.	A WD01