

修订	标记	修改摘要	签名	日期
REV	AO	NEW DWG		2016-03-12








- 1.材料
A.主体: LCP, 黑色, UL 94-V0;
B.端子: 铜合金, 电镀刷金;
C.外壳: 不锈钢, 镀全镍;
- 2.主要特性
A.电压等级: 20V AC;
B.电流: 3A;
C.工作温度: -40℃~85℃;
- 3.电气要求:
A.接触电阻: 40mΩ Max (初始), 50mΩ Max (最后);
B.电压: 100V AC 1分钟;
C.绝缘电阻: 100MΩmin。DC 500v;
- 4.机械性能:
A.插入力: 5~20N。(从1~10,000次);
B.拔出力: 8~20N。(从1~1,000次);
6~20N。(从1,001~10,000次);
C.耐久性寿命: 10,000次;

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

6	SHELL	STAINLESS STEEL SUS201	Ni Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL SUS301	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY C2680	Au G/F /Ni Plated	1SET
2	CONTACT	COPPER ALLOY C2680	Au G/F /Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

HDGC 深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: TYPE C 16板上 外壳长7.35 产品名称: 脚距4.2 脚长1.0 镍AU GF	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: TYPE C-CQ-115PWB
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001



由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作