





由 Autodesk 教育版产品制作



Current Rating: 5A AC,
DC Voltage Rating: 320V AC,DC
Temperature Range: -25°C ~ +85°C
Contact Resistance: 20mΩ Max.
Insulation Resistance: 500MΩ Min.
Withstanding Voltage: 2500V AC/minute
Pin Material: Copper Alloy /Tin-Plated

修订 REV	标记 AO	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
		NEW DWG		2016-03-12

		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话: 0755-27111216 传真: 0755-29940187					
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: SMD PCB 接线端子 产品名称:			
X.X ±0.30	X.X* ±3°	APPD: 核准:		PART NO: 产品编号: HDGC-SMDJX-T02			
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业		DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰		2016-03-12	1:1	mm	A001