






产品名称	SMA 弯式印制面板插座	型号	KH-SMA-KWE17-G
电气性能: 1. Impedance特性阻抗: 50 Ω 2. VSWR电压驻波比: ≤1.5 3. Frequency range频率范围: DC-6GHz 4. Withstanding Voltage耐压: ≥1500V 5. CR接触电阻: 内导体: ≤3m Ω; 外导体≤2m Ω 6. Insulation resistance绝缘电阻: ≥5000M Ω			
机械性能: 1. Center contact withdrawal force内导体分离力: ≥0.28N 2. Recommended mating torque建议适配扭矩: 0.8~1.13N · m 3. Mating cycles机械寿命: ≥500 4. Assembly torque组合部件扭力≥0.5N · m			
环境性能: 1. Operating temperature range工作温度: -40~+85℃ 2. Storage temperature range储存温度: +-30℃~+60℃ 3. 防水要求: 是 4. 满足ROHS要求			
材料与表面处理: 1. Center conductor中心导体: 黄铜镀金(HPb59-1) 2. Outer conductor外导体: 黄铜镀金(HPb59-1) 3. Dielectric介质: 聚四氟乙烯(PTFE)			
其它: 1. Wave solder resistance波峰焊耐热性: 240~250℃ , 5S 2. Packing Standard包装: 100/袋 3. Warranty质保: 6个月			

Kinghelm®



SMA-KWE17牙



技术要求:

1. 未注公差按±0.2
2. 镀层均匀、光滑、无污渍、刮伤.
3. 材料需符合RoHS要求。

型 号:	KH-SMA-KWE17-G	深圳市金航标电子有限公司 SHENZHEN KINGHELM ELECTRONIC CO.,LTD.	
日 期:	2022. 05. 25		
图 号:		绘 图:	
		审 核:	

版本	修改内容	修改人	日期

