








ROHS



PAD AREA

KEEP OUT AREA

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

一、材质和镀涂

- 1、胶芯：LCP,UL 94V-0, 黑色
- 2、端子 磷铜 C5210-H, T=0.15 镍底镀金
- 3、外壳不锈钢 SUS304 T=0.2

二、技术参数


接触电阻: 100MΩ MAX
绝缘阻抗: 1000MΩ MIN(500DC)
额定电流: 每个接触件 1A MAX
额定电压: 30V MAX(DC)
耐压: 500V R.M.S/MIN
使用温度: -40°C~85°C
湿度: 90%~95%
寿命: >5000 次

MICRO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A

COSTOMTER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING		TITLE SIM卡卡座T1.8（翻盖式） REV. A				
CHECK						
APPROVAL						
TOLERANCES ARE		PART NO.	LAIL-SIM05-T1.8-F	UNITS	mm	
30-150	±0.35					ANGLE
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		DWG.NO.		Projection		

ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE



NOTES


1.每卷包装数量:1200PCS/每卷

2.卷带包装方式:




3.每箱包装数量:12000PCS/箱


4.纸箱350mm*350mm*440mm(内部尺寸),材质K=K



上下各1PCS珍珠棉



胶纸工字型封箱



COSTOMER DRAWING			 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	SIM卡卡座T1.8（翻盖式）	REV.	A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-SIM05-T1.8-F	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			DWG.NO.		Projection	