



1. External Dimensions (Unit:m/m)



TYPE	METRIC	A	B	C	D	Q'Ty/Reel
AFB1608	0603	1.6±0.2	0.8±0.2	0.8±0.2	0.3±0.2	4000

2. Construction



NO	PART	MATERIAL
1	Ferrite Body	Fe ₂ O ₃
2	Silver electrode	Ag
3	Silver electrode	Ag
4	Plating	Ni
5	Plating	Sn

3. Part Number Code

AFB 1608 T 601 P15
 A B C D E

A: Series Name Multilayer Ferrite Chip Beads
 B: Dimensions(mm) 1608: 1.6x0.8x0.8
 C: Tolerance T: ±25%
 D: Impedance 601=600Ω
 E: Internal controls

4. Electrical Characteristics

Part Number	Impedance (Ω±25%)	Test Freq. (MHz)	RDC (Ω)Max.	Rated Current (mA)Max.
AFB1608T601P15	600	100 MHz	0.15	1500.0

Curve:

