







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20M Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Copper Alloy
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
XY-PZ2.54V-02-02P	2*1	0.00	2.54
XY-PZ2.54V-02-04P	2*2	2.54	5.08
XY-PZ2.54V-02-06P	2*3	5.08	7.62
XY-PZ2.54V-02-08P	2*4	7.62	10.16
XY-PZ2.54V-02-10P	2*5	10.16	12.70
XY-PZ2.54V-02-12P	2*6	12.70	15.24
XY-PZ2.54V-02-14P	2*7	15.24	17.78
XY-PZ2.54V-02-16P	2*8	17.78	20.32
XY-PZ2.54V-02-18P	2*9	20.32	22.86
.....			
XY-PZ2.54V-02-80P	2*40	(PIN-1)X2.54	(PIN)X2.54

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	CHK.	TITLE: 2.54PH H2.5 2xNPIn 180 μ PC3.0 PA6.0 PB2.5 L11.5 6T	
.X ± 0.35	X.* $\pm 5^\circ$	Alex	Jack	DWG NO. XY-PZ2.54V-02-NP	
.XX ± 0.25	.X.* ± 1			PROJ.  CUSTOMER DRAWING	
.XXX ± 0.2	.XX.* ± 0.5	Can		SIZE A4	SCALE 1:1
				SHEET 1/1	REV. A