




版次 (Edition)	变更摘要 (Change The Content)	日期 (Date)
0	新产品发行 (The first edition)	2016/9/25
1	料号更新 (Material number update)	2024/12/07

技术指标 (Technical Index):

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
- 温度范围 (Temperature range): -25° C ~ 85° C.
- 额定电压 (Rated voltage): 125V, AC/DC.
- 接触电阻 (Contact resistance): ≤ 0.02Ω.
- 绝缘电阻 (Insulation resistance): ≥ 100MΩ.
- 额定电流 (Rated Current): 适用电线型号: a. AWG#28: 1.5A (per pin)
b. AWG#30: 1.0A (per pin)
c. AWG#32: 0.8A (per pin)

7. 产品料号 (Product material No.):

WT125J1W-***-***

NO OF CKT (产品PIN数) 流水码 (Serial number)
Plating (电镀方式) Packing (包装方式)
1: 端子全金 (Terminal G/F OVER ALL) P: PE袋装
3: 端子全亮锡 (Terminal all bright tin) R: TAPE & REEL 卷装

CKT	DIM A	DIM B	DIM C	DIM D
2	1.25	3.87	7.40	0.00
3	2.50	5.12	8.65	0.00
4	3.75	6.37	9.90	2.50
5	5.00	7.62	11.15	3.75
6	6.25	8.87	12.40	5.00
7	7.50	10.12	13.65	6.25
8	8.75	11.37	14.90	7.50
9	10.00	12.62	16.15	8.75
10	11.25	13.87	17.40	10.00
11	12.50	15.12	18.65	11.25
12	13.75	16.37	19.90	12.50
13	15.00	17.62	21.15	13.75
14	16.25	18.87	22.40	15.00
15	17.50	20.12	23.65	16.25
16	18.75	21.37	24.90	17.50
17	20.00	22.62	26.15	18.75
18	21.25	23.87	27.40	20.00
19	22.50	25.12	28.65	21.25
20	23.75	26.37	29.90	22.50

ZGWD 浙江温达电子有限公司
ZHEJIANG WENDA ELECTRONICS CO., LTD

品名 (TITLE)	1.25 Pitch J型卧式WTB 1.25 Pitch Type-J R/A WTB	制图 (DR)	ANLAN
料号 (DWG.NO)	WT125J1W-***-***	校对 (CHKD)	田峰
比例 (SCALE)	单位 (UNITS) mm	审核 (APPD)	黄志明
		张数 (SHEET)	1 OF 1
		SIZE	A4
		REV	A



一般公差 (TOLERANCE)
X ±0.50 .XX ±10
X ±0.20 .XXX ±05
ANGLES ±1°