




SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:30mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PBT
Max.Processing Temp: 180°C for 30-60 seconds
(200°C for 10 seconds)



Dimension antitheses list	
ITEM	A
Standard	4.00

Ordering Information

HC-CZ 254	- *	- N	- Z	- *	- **	- *
No. of Rows 2= Dual Row 3= Three Row 4= Four Row	No. of Pins 10/16/20Pin 32/44/48Pin 64Pin	Type 2-直针 4-弯针	Length (mm) (塑料)	Contact Plating G0: Gold Flash G1: 1u" Gold G2: 3u" Gold G3: 5u" Gold G4: 10u" Gold G5: 15u" Gold G6: 30u" Gold S0: Gold Flash/Tin S1: Tin	Contact Type F= female M= male	

GENERAL TOLERANCE			制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD		
DIM		TOL	审核 CHECK	产品名称 TITLE	欧式插座2.54 双排 直公座	版本 REV.
X. X		±0.30	批准 APPROVAL	产品料号 PART NO.	HC-CZ254-2-N-Z-11.5-XX-M	单位 UNITS
X. XX		±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET
X. XXX		±0.10	投影 Projection			1/1
Angle		±3.0°				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE				