







ABIDE BY ROHS

ITEM	H	
01	3.5	
02	3.8	
03	4.3	
04	4.5	
05	5.0	
06	5.5	
07	6.0	
08	6.5	
09	7.0	
10	7.5	
11	8.0	
12	8.5	
13	9.0	
14	...	

* Key size





P. C. B. Layout



Remarks:

1. Rated current、Voltage: DC 12V 50mA
2. Contact resistance: $\leq 50m\Omega$
3. Insulation resistance: $\geq 100M\Omega$
4. The intensity of operations: $160 \pm 50gf$
5. Life requirements: 100000 times
6. Withstand voltage: AC250V 1 minute
7. All materials comply with RoHS standards



Remarks:

1. Braiding process, can not be caused by carrying half crushed;
2. Pay attention to the direction of the tape, with a clockwise direction out of the carrier tape, with a hole in the top or right

5	Button	PPA	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	4	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		X ≤ 1	±0.05		
设计 DESIGN		1 ≤ X ≤ 5	±0.10	产品名称 TITLE	轻触开关
审核 CHECKED		5 ≤ X ≤ 10	±0.15	产品型号 MODEL	4.5*4.5贴片
校准化 STANDARD		X > 10	±0.25	产品编码 PART NO	ES411X-10XX-XXX-16-B
批准 APPROVALS		重量 WT.		视角 PROJ	
		产地 PRODUCTION		比例 SCALE	:
				页码 SHEET	1 OF 1

ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	--------------	---------	--------	--------