





ABIDE BY ROHS



ITEM	H	
01	3.8	
02	4.5	
03	4.8	
04	5.0	
05	5.5	
06	6.0	
07	6.5	
08	7.0	
09	7.5	
10	8.0	
11	...	
12	10.0	



CIRCUIT DIAGRAM



PCB.circuit prohibited area



Remarks:

- 1.Rated current, Voltage: DC 12V 50mA
- 2.Contact resistance: $\leq 100\text{m}\Omega$
3. Insulation resistance: $\geq 100\text{M}\Omega$
- 4.The intensity of operations: $260 \pm 50\text{gf}$
- 5.Life requirements: 100000次
- 6.Withstand voltage: AC 250V 1分钟
- 7.All materials comply with RoHS standards

5	Button	PPA	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	4	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE	 浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		X ≤ 1 ± 0.05		
设计 DESIGN		1 ≤ X ≤ 5 ± 0.10	产品名称 TITLE	轻触开关
审核 CHECKED		5 ≤ X ≤ 10 ± 0.15	产品型号 MODEL	4.5*4.5*H插脚
校准化 STANDARD		X > 10 ± 0.25	产品编码 PART NO	ES410X-10XX-XXX-26-A
批准 APPROVALS		重量 WT.	视角 PROJ	比例 SCALE
		产地 PRODUCTION		页码 SHEET
				1 OF 1

ECN NO.	REV	DATE.	NEW	CHANGE.	CHECK.	APPRO.
			DESCRIPTION.			