




RoHS Compliant

更改 REV	设计内容 MODIFICATION	日期 DATE	制图 DRAW	核准 APPROVE
A	图面发行	2012/10/29	JY LEE	HERMAN



NOTE:

MATERIAL:

1. TERMINAL: COPPER ALLOY

2. HOUSING: LCP UL 94V-0. COLOR: BLACK

MECHANICAL REQUIREMENT:

1. DURABILITY: 100 CYCLES MIN.

2. INSERTION AND EXTRACTION FORCE: 40N MAX & 11.5N M-ENVIRONMENTAL:

1. CONTACT RESISTANCE: 20 MILLIOHMS MAX INITIAL.



2. DIELECTRIC WITHSTANDING VOLTAGE: 300V AC/MIN.

3. OPERATION: -40°C~+85°C.


4. STORAGE: -55°C~+105°C.

5. REFLOW SOLDERING TEMPERATURE: 255~265° MAXIMUM FOR 5~10 SECONDS.

6. ROHS COMPLIANT





PCB LAYOUT




PART NUMBER: SFP-20P-00

GOLD PLATING U"
0-1U" 1-3U" 2-6U"
3-15U" 4-30U"

PLASTIC MATERIAL
0-LCP BLACK



MATING PCB



QC : Inspection Item	CPK : Cp/Cpk and SPC Control Item	DIMENSION IN mm [Inch]		 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD													
		TOLERANCE UNLESS OTHERWISE SPECIFIED		料号 PART NO:		图号 DWG NO.											
				SFP-20P-00		SFP-20P-00											
		.X± 0.25	X*± 1°	名称 TITLE SFP 20P Connector													
		.XX± 0.20	.X*± 0.5°														
		.XXX± 0.15															
核准 APPROVE		审核 CHECK		制图 DRAW		角法 PROJ.				页数 SHEET		1 / 1					
				JY LEE		比例 SCALE		1:1		图幅 SIZE		A3		更改 REV		A	

If you have any questions, Don't hesitate to email sales@l45jack.com, please!