








PANEL CUT-OUT

Rating :

15A 250V AC T105 UL cUL
10A 250V AC 3C TUV

Insert And Extract Force: 1.36kgf~6.8kgf

Operating Life: ≥5000 cycles

Withstand Voltage: Between all terminals:2500VAC (50-60Hz)1min
terminals to Base:3750V AC (50-60Hz)1min
Leakage Current : 1mA

Insulation Resistance: ≥100MΩ 500V DC

Body Materil: PBT 94V-2~0

A4				普通公差	深圳市华灿天禄电子有限公司					
A3				COMMON TOLERANCE :						
A2				UP TO 5	±0.20	单位	mm	投影	品名	Ac Inlet
A1				ABOVE 5 TO 30	±0.30	UNIT		PROJECTED	PRODUCT NAME	比例
				ABOVE 30	±0.50	绘图		核对	型号	Free
				ANGULAR	±5°	DRAWN BY		核准	料号	DB-F
REV.	DATE	REVISION DESCRIPTION	ISSUE			日期		核准	料号	DB-F-1
						DATE		APPROVAL BY	PART NO.	