





| 修 改 | 記 號 | g | 容 | 修改者 | 日期 |
|-----|-----|---|---|-----|----|
|     | 1   |   |   |     |    |
|     | 2   |   |   |     |    |



#### Specification

- . **Rating** : Voltage 42V 100mA (Switching)  
400mA (None-Switching)
- . **Contact Resistance** : 80mΩ Max
- . **Insulation Resistance**: 100MΩ Min
- . **Operating Force** : 120gf±30gf
- . **Life Cycle**: 25,000 steps
- . **Solder Condition** : Reflow Soldering : 10s/260 °C  
Iron Soldering : 3s/350°C  
Wave Soldering : 5s/280°C

|                                            |   | Real Code |   |   |   |   |
|--------------------------------------------|---|-----------|---|---|---|---|
|                                            |   | C         | 1 | 2 | 4 | 8 |
| 10<br>P<br>o<br>s<br>i<br>t<br>i<br>o<br>n | 0 | ●         |   |   |   |   |
|                                            | 1 | ●         | ● |   |   |   |
|                                            | 2 | ●         |   | ● |   |   |
|                                            | 3 | ●         | ● | ● |   |   |
|                                            | 4 | ●         |   |   | ● |   |
|                                            | 5 | ●         | ● |   | ● |   |
|                                            | 6 | ●         |   | ● | ● |   |
|                                            | 7 | ●         | ● | ● | ● |   |
|                                            | 8 | ●         |   |   |   | ● |
|                                            | 9 | ●         | ● |   |   | ● |
| 16<br>P<br>o<br>s<br>i<br>t<br>i<br>o<br>n | A | ●         |   | ● |   | ● |
|                                            | B | ●         | ● | ● |   | ● |
|                                            | C | ●         |   |   | ● | ● |
|                                            | D | ●         | ● |   | ● | ● |
|                                            | E | ●         |   | ● | ● | ● |
|                                            | F | ●         | ● | ● | ● | ● |

本公司智慧財產，未經同意不得複製  
Without permission, copying is  
strictly prohibited.

|                  |
|------------------|
| 中心孔距<br>皆為±0.05  |
| 一般公差             |
| 0- 150 : ±0.05   |
| >151- 300 : ±0.1 |
| >301- 500 : ±0.2 |
| >501-1000 : ±0.3 |

|    |           |      |     |    |          |
|----|-----------|------|-----|----|----------|
| 製圖 | P.M.D     | 比例   | 5:1 | 日期 | 15/11/05 |
| 設計 | Shane jin | 單位   | mm  | 材質 |          |
| 校對 | Boris jia | 全週倒角 |     | 數量 |          |
| 審核 | Jack Kuo  | 視圖   |     | 處理 |          |

|                                                                                                                                                                   |            |    |  |    |    |        |  |  |  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|----|--|----|----|--------|--|--|--|
| <div> 连兴旺电子(深圳)有限公司</div> <div>LXWCONN ELECTRONICS (SHENZHEN) CO., LTD</div> |            |    |  |    |    |        |  |  |  |
| 圖號                                                                                                                                                                | RBMSDR-10S |    |  | 機型 | RB | Series |  |  |  |
| 設備                                                                                                                                                                |            | 圖名 |  |    |    | 備註:    |  |  |  |