





ABIDE BY ROHS

ITEM	H
01	3.5
02	3.8
03	4.3
04	4.5
05	5.0
06	5.5
07	6.0
08	6.5
09	7.0
10	7.5
11	8.0
12	8.5
13	...
14	10.0

* Key size



线路图
Circuit Diagram

Remarks:

- Rated current、Voltage: DC 12V 50mA
- Contact resistance: $\leq 100\text{m}\Omega$
- Insulation resistance: $\geq 100\text{M}\Omega$
- The intensity of operations: $260\pm 50\text{gf}$
- Open and close the trip: $0.15\pm 0.05\text{mm}$
- Life requirements: 100,000次
- Withstand voltage: AC 250V 1分钟
- All materials comply with RoHS standards

5	Cover	Brass	1	Cu-Sn Plating
4	Shrapnel	SUS	1	Ag Plating
3	Terminal	Brass	2	Ag Plating
2	Button	PPA	1	Black
1	Housing	PPA	1	Black
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE	浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.			
绘图 DRAWN		$X\leq 1$ $1\leq X\leq 5$ $5\leq X\leq 10$ $X>10$ ANGLE	产品名称 TITLE	轻触开关		
设计 DESIGN		± 0.05 ± 0.10 ± 0.15 ± 0.25 $\pm 3^\circ$	产品型号 MODEL	4.5*4.5前插后贴		
审核 CHECKED		图号 DRAWING NO.	产品编码 PART NO	ES414X-10X-XXX-26-B		
校准化 STANDARD		重量 WT.	视图 PROJ	比例 SCALE	页码 SHEET	1 OF 1
批准 APPROVALS		产地 PRODUCTION				

ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	--------------	---------	--------	--------